



B-FLEX ITALIA S.r.l.

Via 1° Maggio, 44
36050 Sovizzo (VI) ITALY
Ph +39 0444.028139
info@b-flexitalia.com

www.b-flexitalia.com

follow us on



GIMME 5 EVO

**BF GIMME5EVO
SPECIAL**



GIMME5 EVO SPECIAL

PRODUCT DESCRIPTION

GIMME5 EVO SPECIAL is available in 5 colors. It's made of Polyurethane with a metallic finish. It can be heat applied on organic or synthetic fibers in just four seconds.

This product is easy to work with; the sticky polyester carrier allows for fast weeding and easy repositioning of details that might have accidentally been removed. It is also soft and comfortable to wear, even with bulky designs.

Its thickness (80 micron) and its elasticity make GIMME5 EVO SPECIAL pleasant and soft on any garment, and ideal for multi-layer applications.

GIMME5 EVO SPECIAL can withstand wash cycles up to 60°C.

APPLICATION INSTRUCTIONS

- Mirror cut GIMME5 EVO SPECIAL with a 45° blade
- Weed GIMME5 EVO SPECIAL and remove all excess material.
- Pre-heat your press to 140°C.
- Place the garment on the lower platen of your heat press.
- Press at 140°C for 4 seconds.
- Peel the carrier

STANDARD SIZES

- H 150 cm => available lengths: 25 mt (upon request)
- H 100 cm => available lengths: 25 mt (upon request)
- H 75 cm => available lengths: 25 mt (upon request)
- H 50 cm => available lengths: 25 mt / 12,5 mt / 5 mt / 1 mt (standard)

APPLICATION TIPS

- Recommended Fibers: organic, synthetic, mixed
- Ideal for layering.
- Can be applied with other B-FLEX films (ex. FATTY, GLITTER, FLOCK, etc.)
- Ability to cut designs as small as 0.1 cm
- Doesn't require a Teflon sheet during the pressing phase.

TECHNICAL DATA

Film:	PU/ Polyurethane
Thickness:	80 μ (±5%)
Carrier:	Adhesive PET

APPLICATION

Temperature:	140°C - 285° F
Time:	4"
Pressure:	medium – 3,5 bar – 50 PSI

LINER REMOVAL

Hot

WASH RESISTANCE

First Wash:	wait 12 hours after application
Max. Wash temp.:	60° C
Dry Clean:	NO
Softener:	YES
Bleach:	NO
Dryer:	YES

SAFETY NOTICE

The values reported in this document are average values as tested under normal conditions in our lab. We cannot provide a guarantee regarding the information abovementioned in this page.

Due to possible variations in the production of garments, B-FLEX recommends testing the material prior to all applications.

This spec sheet is valid for the following products:
GIMME5 EVO SPECIAL. Rev_2019/09_EN